

User Manual

SIG-0 Mini-Gateway

Communication Bridge / Network Adapter




AscenticTM
RETAIL ENGINEERING
by Audio Authority®

Introduction

The SIG-0 Mini-Gateway is a communication bridge that connects a powered RS-232 hub and a TCP socket to facilitate communication between the RS-232 and network devices. The SIG-0 must receive power through the RJ45 serial connection cable from a compatible device such as Model 1798. Configure and store data directly on the device via the integrated microSD port or serial commands. The device can be mounted directly to a flat surface using the mounted flanges.

Features

- Serves as a communication bridge between an RS-232 device and a network device.
- Powered via RS-232 connection (requires compatible power injector such as 1798).
- Able to load, configure, and store information via serial commands or a configuration file on a microSD card.
- Packages incoming RS-232 data for export to the controlled device.
- SIG-0 device is able to be configured via RS-232 port after entering configuration mode.
- LED indicator to confirm network connection.
- Update firmware via microSD.



Configuration Methods

MicroSD Configuration

The SIG-0 accepts configuration commands from a microSD card on boot.

- Create an empty text file in the root directory of a microSD Card titled 'AacConfig.txt'.
- In the AacConfig file, add any configuration commands you would normally send via RS-232 in Configuration mode as a new line (see below).
- Insert the microSD card into the unpowered device, then apply power. The configuration will then be loaded into flash memory on boot until the microSD is removed.

NOTE: You will not be able to use the device until the microSD is removed.

Configuration Mode

Configuration mode allows the device to be configured over an RS-232 port. The following list of commands are accepted: See page 2

Commands:

Name	Description	Format	Response
Enter Configuration	Enables Config Mode	+++	n/a
Exit Configuration	Returns to command mode	[DEV=254;EXIT]	n/a
Query Link Status	Ethernet link up/down	[DEV=254;NET;LINK?]	[DEV=254;NET;LINK=UP]
Query IP Address	Returns the SIG-0's current IP Address	[DEV=254;NET;LINK;IP?]	[DEV=254;NET;LINK;IP=10.0.0.2]
Query Server TCP Port	Returns currently set Server TCP Port	[DEV=254;NET;SERVER;PORT?]	[DEV=254;NET;SERVER;PORT=23]
Set Server TCP Port	Changes the target Server Port	[DEV=254;NET;SERVER;PORT=23]	n/a
Reset Defaults	Resets the SIG-0 to factory defaults	[DEV=254;RESET;DEFAULT]	n/a
Reboot Device	Reboots the SIG-0 to implement change	[DEV=254;REBOOT]	n/a

NOTE: All commands except "Enter Configuration" should be terminated by a carriage return. Some set commands require a device reboot to take effect. Not all commands will have an associated response. Full command set is available upon request. It is recommended to reboot the SIG-0 after any configuration changes. This can be done serially, and after reboot, the device will be in Configuration Mode by default.

Communication

Serial Port (RS-232)

The SIG-0 communication bridge has the default device ID 254. It can send and receive serial commands via RS-232 at 115200 Baud, 8-N-1, and full-duplex. The port may be set for null or straight using the switch located on the side of the device opposite the microSD port. The port is a modular RJ-45 jack with the following pinout:

RJ-45 Pinout:

Pin #	Function	Pin #	Function
P1	Orange White - Ground	P5	+12V DC Power
P2	Orange - Ground	P6	Green - RX or TX
P3	Green White - TX or RX	P7	Brown White - Ground
P4	+12V DC Power	P8	Brown - Ground

Quick Start Instructions

- Connect the SIG-0 RS-232 port to another RS-232 device with a power injector (e.g. Model 1798).
- Ensure that settings have been configured correctly for both devices. (This can be done serially or via an SD Configuration update.)
- Connect the SIG-0's Ethernet port to the device to be controlled and power on both devices.
- Ensure that the Ethernet LEDs are both illuminated, and the power LED is blinking steadily. (The connected network device will be assigned an IP address of 192.168.0.2 by DHCP, unless configured otherwise.)
- Communicate directly with the end device.

Troubleshooting

No RS-232 communication:

- Ensure connections are fully seated.
- Ensure devices are using the correct protocol settings.
- Ensure the Null/Straight selector is set correctly.

No Ethernet Connectivity Lights

- Ensure connections are fully seated.
- Ensure the End Device is powered on with Ethernet enabled.
- Power cycle all devices to clear out previous TCP connections.

LED periodically blinks fast (no TCP Socket connection)


- Ensure connections are fully seated.
- Ensure both the SIG-0 and end devices have been configured correctly.
- Power cycle all devices to clear out previous TCP connections.*

**Some devices have a limitation on the number of connected TCP clients, and may require a delay period or reboot to clear.*

Example System:

SIG-0 Bridge Between RS-232 and Network

This display utilizes a SIG-0 communication bridge to connect a media device with an RS-232 to a network. Commands stored on the SIG-0 are used to automate run times for the device.



Firmware Update Process

The SIG-0 communication bridge is updatable via the microSD port on the side of the module:

- Copy new firmware “.FWU” file onto a blank microSD Card (FAT).
- Insert Firmware Update SD into the device with device power disconnected.
- Apply power to device, monitoring the power LED Indicator.
- When power LED indicator returns to a slow blink, update is complete.
- To verify the firmware update, send the firmware version query listed in the Commands List (see above) and ensure response matches the firmware version expected.

Product Specifications

Inputs and Outputs

Standard Inputs: 1x microSD Card

Standard In/Out: 1x RS-232 Port w/ Null/Straight Switch (RJ-45), 1x Ethernet Port (RJ-45)

Indicators: 1x Green Power Heartbeat/Connection Indicator

Power Input Specification

Power Entry Port: 1x RJ-45 via RS-232 Port

Voltage: 12V DC

No-Load Current: 60mA

Maximum Load Current: 80mA

Mechanical Details

Case Type: Molded ABS with Cutouts

Case Dimensions (Inches, WxLxH): 3.00 x 2.00 x 1.49

Case Dimensions (millimeters, WxLxH): 76.20 x 50.80 x 37.85

Mounting Locations: Molded Flanges

